

Q1 2025

• Opto-Electronic

- ESL-10G-SR
- ESL-10G-BR
- RCP-LR4

• Interconnect

- POF M29504 (update)
- Lightly (update)
- Potted Connectors/QSFPs

• Optical Sub-Assembly

- 1-10/14-28G MM ROSA
- 1-28G CWDM4 TOSA

• Test

- SPOT Eval Boards

Q2 2025

• Opto-Electronic

- SPOT-SR4
- SPOT-CE-SR4

• Interconnect

- MT-T Connector
- Lensed MT Cable Assemblies

• Optical Sub-Assembly

- 1-28G CWDM TOSA
- SM FP TOSA/ROSA

• Test

- Custom OITs

Q3 2025

• Opto-Electronic

- SFP28 SR, LR
- SPOT28-SR
- SPOT28-CE-SR

• Interconnect

- MT-x Jumpers
- Rugged SM/MM Couplers

• Optical Sub-Assembly

- 1310 Defocused FP TOSA
- 31/55 & 27/33 BOSA

• Test

- OptoCube 10G (updates)

Q4 2025

• Opto-Electronic

- RJ-10G-SWDM
- ESL-10G-SWDM

• Interconnect

- S/C/D/WDM Multiplexers
- Rugged Singlemode /Multi-Fiber Termini

• Optical Sub-Assembly

- 1/10/40Gbps Optical Engine
- 10/28Gbps Optical Engine

• Test

- FPGA Based Eval Boards

For more information about COTSWORKS products, please contact our sales support team.

• Americas & Asia/Pacific | 440-446-8800 | sales@cotsworks.com

• EMEA | +49(0) 661 9786 9200 | EMEAsales@cotsworks.com