

OPTO-ELECTRONIC PRODUCT PLATFORM


Rugged Fiber Optics for Harsh Environments



OPTO-ELECTRONIC PRODUCT PLATFORM

The Moog Opto-Electronic Product Platform consists of optical transceivers designed to operate in the harsh environments of commercial, military aerospace, and industrial applications. The opto-electronic transceivers are engineered and tested to meet parameters defined within MIL-STD-883 and MIL-STD-810 to achieve optimal performance across wide temperature ranges, and the demanding shock, vibration and humidity requirements of a ruggedized environment. The sub-components are selected for their robust and long life cycles, increasing each transceivers' operational life span and their Mean Time To Failure rating. Moog's Opto-Electronic Product Platform utilizes a custom-off-the-shelf approach to create a suitable solution to meet any networking requirements and reduce total cost of ownership.

Rugged Pluggable Optical Transceivers




- Quad ARINC 801 optical interface
- Multiple TX and RX configurations
- 1-28 Gbps MM or SM
- Electrically pluggable




- Dual ARINC 801 optical interface
- Duplex, dual TX/RX, BiDi configurations
- 1-28 Gbps MM or SM
- Electrically pluggable

Solder-Down Optical Transceivers




- Dual LC/dual ARINC 801 option optical interface
- Duplex, dual TX/RX configurations
- 1-28 Gbps MM or SM
- Surface mount electrical connector



- Dual LC/dual ARINC 801 option optical interface
- Duplex, dual TX/RX, BiDi configurations
- 1-4 Gbps MM or SM
- Thru-hole electrical connector

Hot Swappable Optical Transceivers



- Dual LC optical interface
- Duplex, dual TX/RX, Bi-Di configurations
- 1-28 Gbps MM or SM
- SFP+MSA compliant Envelope per SFF-8432




- MPO/Pigtailed optical interface
- 4TX/4RX configuration
- 1, 10, 40, 100 Gbps MM
- QSFP+ compliant to SFF-8436
- QSFP28 compliant to SFF-8661

Parallel Optical Transceivers (High Density)



- MT ferrule optical interface w/secure MT-R CLAMP
- 4TX/4RX configuration
- 1/10/40 Gbps MM
- Ruggedized electrical QSFP card-edge connector



- MT-T optical interface
- 4TX/4RX configuration
- 1/10/40 Gbps MM
- Ruggedized electrical QSFP card-edge connector

MOOG

Moog's Product Platforms include Opto-Electronic, Interconnect, Test Equipment and Optical Sub-Assemblies. For more information regarding any of these product lines, please reach out to cotsworkssales@moog.com.