

ELEMENTAL VISUAL PRODUCT GUIDE



ESL 28G-LR4 CWDM													MT-T MT TAB SM & MM	CB C-BEAM MM	HD HIGH DENSITY CABLING SM & MM	SHP SHIPBOARD SM & MM	MIL D38999 SM & MM					
ESL 28G-SR 850nm													MT-T MT TAB KIT SM & MM	ELIO ARINC 801 2.5mm SM & MM	MMF MULTI MODE FIBER 50/62.5µm	PTFE TEFLON SM & MM	µM MICRO D38999 SM & MM					
ESL 10G-SR-DX 850nm	RCP 28G-SR 850nm	RCP 10G-SX-TX 850nm	SPOT CE: Card Edge 850nm													COM COMMERCIAL ST, FC, SC	A801 ARINC 801 1.25mm SM & MM	MT EXPANDED BEAM SM & MM	29504 POF M29504 SM & MM	MMF+ MULTI MODE FIBER 100/140µm	PVC CHLORIDE SM & MM	A600 ARINC 600 SM & MM
ESL 10G-SR-TX 850nm	RCP 10G-LR4-DX CWDM	RCP 10G-SX-RX 850nm	SPOT MB: Mid-Board 10/28G 850nm	RJ 10G-LR4 CWDM	RJ 28G-SR 850nm	RJ 3G-EX 1310nm	RJ 3G-SDI-LX 850nm	SFP28 25G-SR 850nm	SFF 3G-TX2 850nm	SFB 3G-35/53 1310/1550nm	HM HERMETIC POTTED CONN SM & MM	LC LC CONNECTOR SM & MM	A801 LIGHTLY™ SM & MM	MT BREAKOUT SM & MM	29504 M29504/4&5 SM & MM	SMF SINGLE MODE FIBER 5µm-9µm	PE POLYETHYLENE SM & MM	TF TFOCA SM & MM				
ESL 10G-SR-RX 850nm	RCP 10G-LR4-TX CWDM	RCP 5G-SX-DX 850nm	SPOT MB: Mid-Board 1/10/40G 850nm	RJ 10G-CWDM CWDM	RJ 10G-SX 850nm	RJ 3G-LX 1310nm	RJ 3G-SDI-TX2/RX2 850nm	SFP 1G-SX/LX 850nm	SFF 3G-RX2 850nm	SFB G-35/53 1310/1550nm	IC INTERPOSER CARD ASSEMBLY RJ/RCP/SFF/SFB	LC-R LC RUGGED SM & MM	A801 POF SM & MM	MT MTP/MPO SM & MM	29504 M29504/14&15 SM & MM	PLX SIMPLEX/DUPLEX SM & MM	POF PLASTIC OPTICAL FIBER 1mm	NAV M28876 SM & MM				
ESL 10G-BR10-23 1270/1330nm	RCP 10G-LR4-RX CWDM	RCP 5G-SX-TX 850nm	QSFP 28G 850nm	RJ 10G-DWDM PIN C-BAND 850nm	RJ 10G-TX2/RX2 850nm	RJ 3G-ZX 1550nm	RJ 1G-DX 1310nm	SFP+ 10G-SR 850nm	SFF 4G-SX-DPLX 850nm	SFB G-BX10 1310/1550nm	PT PIGTAIL ASSEMBLY RJ/RCP/SFF/SFB	LC-T LC TAB SM & MM	LC-801 LOCKING TAB ARINC 801 ADAPTER SM & MM	VITA 66 & 87 SM & MM	29504 M29504/20&21 SM & MM	CPLX COMPLEX/MULTI-CH SM & MM	PMMA ACRYLIC 50µm-1mm	EN EN4165 SM & MM				
ESL 10G-BR10-32 1270/1330nm	RCP 10G-SX-DX 850nm	RCP 5G-SX-RX 850nm	QSFP 1/10/40G 850nm	RJ 10G-DW-E APD C-BAND 850nm	RJ 5G-SX(-C) 850nm	RJ 3G-TX2/RX2 850nm	RJ 155M-FX-DPLX 1300nm	SFP+ 10G-LR 1310nm	SFF 4G-LX-DPLX 1310nm	SFB M-35/53 1310/1550nm	LAC 10G-SR-TX/RX 850nm	LC-T DUPLEX SM & MM	LC-T801 METAL LATCH ARINC 801 ADAPTER SM & MM	MT MECHANICAL TRANSFER SM & MM	JMS/P JEWEL SOCKET JEWEL PIN SM & MM	RIBN RIBBON FIBER SM & MM	HYB HYBRID ASSEMBLY COPPER/FIBER	EPX EN4644 SM & MM				

4-CHANNEL PLUGGABLE: RCP™	2-CHANNEL SOLDERED: RJ	TERMINI
2-CHANNEL PLUGGABLE: ESSENTIAL™	2-CHANNEL SOLDERED: SFF 1-CHANNEL SOLDERED: SFB	FIBER & JACKETING
2-CHANNEL PLUGGABLE: SFP	HYBRID ASSEMBLY	OPTICS
8-CHANNEL PLUGGABLE: SPOT™/QSFP	CONNECTORS	TEST EQUIPMENT

TOSA OPTICAL SUB ASSEMBLY TX	ROSA OPTICAL SUB ASSEMBLY RX	BOSA OPTICAL SUB ASSEMBLY BI-DI	PKG CHIP ON BOARD CUSTOM DESIGN	LENS GRIN/BALL ASPHERE FIBER	VCSEL VERTICAL CAVITY SURFACE EMITTING LASER	FP FABRY PEROT LASER	EML EXTERNALLY MODULATED LASER	DFB DISTRIBUTED FEEDBACK LASER	LED LIGHT EMITTING DIODE	APD AVALANCHE PHOTODIODE	PIN PIN DIODE	TIA TRANS IMPEDENCE AMPLIFIER DIE	
			OIT OPTICAL INTEGRATED TEST PLATFORM SM & MM	SFP+ 802.3cz 980nm	LS LIGHTNING STICK 1G ETHERNET	OC OPTO-CUBE 10G ETHERNET	VFL VISUAL FAULT LOCATOR VFL-SFP	RMS RUGGED MECHANICAL SPLICE SM & MM	MUX LR4, SWDM, CWDM, DWDM SM & MM	3155 OPTICAL SPLITTER SM & MM	EVAL EVALUATION BOARD SM & MM	LI LUCIOL INSTRUMENTS OTDR	KI KINGFISHER INTERNATIONAL PM / LS
AS 9100	ISO 9001	MIL STD 810	MIL STD 883	NIST	ITAR	FDA CLASS 1 LASER EYE SAFETY	ARINC	SOSA	SAE	EN	ATEX		

AMERICAS
749 Miner Rd., Highland Heights, OH 44143
26301 Curtiss Wright Pkwy., Richmond Heights, OH 44143

EUROPE
Am Alten Schlachthof 4, 36037 Fulda, Germany

www.cotsworks.moog.com